

## Stainless steel minicylinders CETOP RP52-P DIN/ISO 6432 - Series 94 e 95

Product code: 94N2A20A068

Datasheet creation date: 07/03/2025 17:26

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                        |                                                    |
|------------------------|----------------------------------------------------|
| <b>Series</b>          | 94                                                 |
| <b>Diameter (mm)</b>   | 20                                                 |
| <b>Version</b>         | N = standard                                       |
| <b>Operation</b>       | 2 = double-acting (front and rear cushions)        |
| <b>Materials</b>       | A = stainless steel AISI 316 (SS 2343), joints NBR |
| <b>Construction</b>    | A = standard                                       |
| <b>rod seals viton</b> | -                                                  |
| <b>Stroke type</b>     | variable                                           |
| <b>Stroke (mm)</b>     | 68                                                 |

## Stainless steel minicylinders CETOP RP52-P DIN/ISO 6432 - Series 94 e 95

Product code: 94N2A20A068



### DIMENSIONS

|                  |         |
|------------------|---------|
| <b>A (mm)</b>    | 8       |
| <b>AM (mm)</b>   | 20      |
| <b>BE</b>        | M22x1,5 |
| <b>Ø CD (mm)</b> | 8       |
| <b>D (mm)</b>    | 26.2    |
| <b>EE</b>        | G1\8    |
| <b>EW (mm)</b>   | 16      |
| <b>KK</b>        | M8x1,25 |
| <b>KW (mm)</b>   | 5       |
| <b>(mm)</b>      | 5       |
| <b>L (mm)</b>    | 12      |
| <b>L1 (mm)</b>   | 116     |
| <b>L2 (mm)</b>   | 59      |
| <b>L3 (mm)</b>   | 17.5    |
| <b>L4 (mm)</b>   | 8.0     |
| <b>L5 (mm)</b>   | 19      |
| <b>SW (mm)</b>   | 7       |
| <b>WF (mm)</b>   | 24      |
| <b>XC (mm)</b>   | 95      |