

## - CX configurator

Product code: CX04-A-Q

Datasheet creation date: 07/03/2025 16:17

Check the most updated document online [click here](#)



### TECHNICAL DATA

|   |                               |
|---|-------------------------------|
| <b>Serie</b>                                    | CX                            |
| <b>Elettrical connection</b>                    | CX04=ETHERNET/IP              |
| <b>8 digital inputs</b>                         | A = 8 digital inputs M8       |
| <b>4 digital inputs</b>                         | 0 = No module                 |
| <b>2 IN 4-20 mA</b>                             | 0 = No module                 |
| <b>2 IN 0-10V</b>                               | 0 = No module                 |
| <b>1 in 4-20 mA + 1 IN 0-10 V</b>               | 0 = No module                 |
| <b>4 M12 duo digital outputs</b>                | Q = 4 M12 duo digital outputs |
| <b>2 OUT 4-20 mA</b>                            | 0 = No module                 |
| <b>2 OUT 0-10 V</b>                             | 0 = No module                 |
| <b>1 OUT 4-20 mA + 1 OUT 0-10 V</b>             | 0 = No module                 |
| <b>1 OUT 4-20 mA + 1 IN 0-10 V</b>              | 0 = No module                 |
| <b>1 OUT 4-20 mA + 1 IN 4-20 mA1 OUT 0-10 V</b> | 0 = No module                 |
| <b>1 OUT 0-10 V + 1 IN 0-10 V</b>               | 0 = No module                 |
| <b>1 OUT 0-10 V + 1 IN 4-20 mA</b>              | 0 = No module                 |
| <b>Initial subnet module</b>                    | 0 = No module                 |

## - CX configurator

Product code: CX04-A-Q

### **DIMENSIONS**

|                                     |                               |
|-------------------------------------|-------------------------------|
| <b>Serie</b>                        | CX                            |
| <b>Electrical connection</b>        | CX04=ETHERNET/IP              |
| <b>8 digital inputs</b>             | A = 8 digital inputs M8       |
| <b>4 digital inputs</b>             | 0 = No module                 |
| <b>2 IN 4-20 mA</b>                 | 0 = No module                 |
| <b>2 IN 0-10V</b>                   | 0 = No module                 |
| <b>1 in 4-20 mA + 1 IN 0-10 V</b>   | 0 = No module                 |
| <b>4 M12 duo digital outputs</b>    | Q = 4 M12 duo digital outputs |
| <b>2 OUT 4-20 mA</b>                | 0 = No module                 |
| <b>2 OUT 0-10 V</b>                 | 0 = No module                 |
| <b>1 OUT 4-20 mA + 1 OUT 0-10 V</b> | 0 = No module                 |
| <b>1 OUT 4-20 mA + 1 IN 0-10 V</b>  | 0 = No module                 |
| <b>1 OUT 4-20 mA + 1 IN 4-20 mA</b> | 0 = No module                 |
| <b>1 OUT 0-10 V + 1 IN 0-10 V</b>   | 0 = No module                 |
| <b>1 OUT 0-10 V + 1 IN 4-20 mA</b>  | 0 = No module                 |
| <b>Initial subnet module</b>        | 0 = No module                 |