

Direct Operated Solenoid Valves with Separation Diaphragm - PDV Series

Product code: PDVC0122-C13GN-M007AC020

Datasheet creation date: 10/03/2025 11:41

Check the most updated document online [click here](#)




TECHNICAL DATA

| | |
|-----------------------------------|--------------------------------------|
| Series | PDV |
| Body execution | C0 = body with interface for subbase |
| Number of ways - functions | 1 = 2/2 way - NC |
| Pneumatic connections | 22 = PDV-type interface, 2-way |
| Orifice diameter | C1 = Ø 2.0 mm |
| Materials held | 3 = FKM |
| Body materials | G = PEEK |
| Manual intervention | N = not foreseen |
| Fixing | M = fixing screws for metal |
| Options | 00 = none |
| Electrical connection | 7A = cables 300 mm |
| Voltage - absorbed power | C020 = 12 V DC - 2 W |

Direct Operated Solenoid Valves with Separation Diaphragm - PDV Series

Product code: PDVC0122-C13GN-M007AC020



DIMENSIONS

| | |
|-----------------------------------|--------------------------------------|
| Series | PDV |
| Body execution | C0 = body with interface for subbase |
| Number of ways - functions | 1 = 2/2 way - NC |
| Pneumatic connections | 22 = PDV-type interface, 2-way |
| Orifice diameter | C1 = Ø 2.0 mm |
| Materials held | 3 = FKM |
| Body materials | G = PEEK |
| Manual intervention | N = not foreseen |
| Fixing | M = fixing screws for metal |
| Options | 00 = none |
| Electrical connection | 7A = cables 300 mm |
| Voltage - absorbed power | C020 = 12 V DC - 2 W |