

## Cylinders with integrated guide - Series QCT QCB

Product code: QCB2A020A050EX

Datasheet creation date: 19/05/2026 09:42

Check the most updated document online [click here](#)




### TECHNICAL DATA

<b>SERIE (Series)</b>	QC
<b>VERSION (Version)</b>	B = linear ball bearings
<b>FUNZ (Operation)</b>	2 = double acting
<b>MAT (Materials)</b>	A = anodized aluminium body, rolled stainless steel 303 piston rod, hardened steel C50 columns for QCB
<b>PHY (Diameter / mm)</b>	20
<b>TYP (Construction)</b>	A = standard
<b>HUB (Stroke / mm)</b>	50
<b>ATEX (Certifications)</b>	EX = ATEX

## Cylinders with integrated guide - Series QCT QCB

Product code: QCB2A020A050EX



### DIMENSIONS

<b>L3 (mm)</b>	75.0
<b>C (mm)</b>	10
<b>B (mm)</b>	22.0
<b>O2 (mm)</b>	44
<b>O4 (mm)</b>	39
<b>A (mm)</b>	10
<b>D (mm)</b>	10
<b>E1 (mm)</b>	70
<b>E2 (mm)</b>	18
<b>F</b>	G 1/8
<b>F1 (mm)</b>	10.5
<b>F2 (mm)</b>	10.5
<b>F3 (mm)</b>	25.0
<b>F4 (mm)</b>	12.5
<b>F5 (mm)</b>	11.5
<b>F6 (mm)</b>	10.5
<b>G1 (mm)</b>	81
<b>G2 (mm)</b>	30
<b>H (mm)</b>	72
<b>H1 (mm)</b>	54
<b>L1 (mm)</b>	37.0
<b>L2 (mm)</b>	53.0
<b>M1 (mm)</b>	83

<b>M2 (mm)</b>	36
<b>N (mm)</b>	24
<b>O1 (mm)</b>	17
<b>O3 (mm)</b>	28
<b>P1</b>	M5x0.8
<b>P2</b>	M5x0.8
<b>P3</b>	M6x1
<b>Q (mm)</b>	13
<b>R (mm)</b>	12
<b>heavy (mm)</b>	6
<b>Y (mm)</b>	28
<b>Y1 (mm)</b>	3
<b>Y2 (mm)</b>	3.5
<b>Y3 (mm)</b>	3
<b>Y4 (mm)</b>	6
<b>X (mm)</b>	5.5
<b>X1 (mm)</b>	9
<b>X2 (mm)</b>	5.0
<b>J (mm)</b>	44
<b>K</b>	M5