

## Short stroke magnetic cylinders - Series QP-QPR

Product code: QP2A063A130

Datasheet creation date: 10/03/2025 00:05

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                        |                            |
|------------------------|----------------------------|
| <b>Series</b>          | QP = standard              |
| <b>Diameter (mm)</b>   | 63                         |
| <b>Operation</b>       | 2=double-acting            |
| <b>Materials</b>       | A = rolled stainless steel |
| <b>Construction</b>    | A = standard               |
| <b>Stroke type</b>     | = variable                 |
| <b>Stroke (mm)</b>     | 130                        |
| <b>Atex</b>            | No Atex                    |
| <b>Rod lenght (mm)</b> | 0                          |

## Short stroke magnetic cylinders - Series QP-QPR

Product code: QP2A063A130



### DIMENSIONS

|               |       |
|---------------|-------|
| A (mm)        | 80.0  |
| B (mm)        | 62.0  |
| B1 (mm)       | 60    |
| B2 (mm)       | 61    |
| $\phi$ C (mm) | 20    |
| D (mm)        | 88.00 |
| E (mm)        | 80.00 |
| G (mm)        | 49.5  |
| G1 (mm)       | 50.1  |
| H1 (mm)       | 13.0  |
| H (mm)        | 13.0  |
| J (mm)        | 8.5   |
| J1            | M12   |
| K (mm)        | 15.0  |
| L (mm)        | 8.5   |
| L1 (mm)       | 31.5  |
| M (mm)        | 13.5  |
| M1 (mm)       | 9.0   |
| N (mm)        | 54.0  |
| N1 (mm)       | -     |
| $\phi$ O (mm) | 50    |
| P             | M8    |
| Q             | G1/4  |

|                |       |
|----------------|-------|
| R (mm)         | 60.0  |
| R1 (mm)        | 62.00 |
| R2 (mm)        | 61    |
| SW (mm)        | 17    |
| T (mm)         | 4.0   |
| U (mm)         | -     |
| V (mm)         | 48.00 |
| AA (mm)        | 12    |
| BB (mm)        | 8.5   |
| $\phi$ CC (mm) | 14.0  |
| $\phi$ DD (mm) | 9.0   |
| EE (mm)        | 15.0  |
| FF             | M6    |
| LL (mm)        | 62.0  |
| MM (mm)        | 80.0  |
| NN (mm)        | 80    |
| RR (mm)        | 62.0  |
| VV (mm)        | -     |
| Z (mm)         | 8.5   |