

## Short stroke magnetic cylinders - Series QP-QPR

Product code: QPR2A080A050

Datasheet creation date: 09/03/2025 23:38

Check the most updated document online [click here](#)




### TECHNICAL DATA

|                        |                            |
|------------------------|----------------------------|
| <b>Series</b>          | QPR = anti-rotation        |
| <b>Diameter (mm)</b>   | 80                         |
| <b>Operation</b>       | 2=double-acting            |
| <b>Materials</b>       | A = rolled stainless steel |
| <b>Construction</b>    | A = standard               |
| <b>Stroke type</b>     | N = standard               |
| <b>Stroke (mm)</b>     | 50                         |
| <b>Atex</b>            | No Atex                    |
| <b>Rod lenght (mm)</b> | 0                          |

## Short stroke magnetic cylinders - Series QP-QPR

Product code: QPR2A080A050



### DIMENSIONS

|          |        |
|----------|--------|
| A (mm)   | 98.0   |
| B (mm)   | 77.0   |
| B1 (mm)  | -      |
| B2 (mm)  | 77     |
| Ø C (mm) | 25     |
| D (mm)   | 104.00 |
| E (mm)   | 98.00  |
| G (mm)   | 57.5   |
| G1 (mm)  | -      |
| H1 (mm)  | 16.2   |
| H (mm)   | 16.2   |
| J (mm)   | M12    |
| J1       | M12    |
| K (mm)   | 17.0   |
| L (mm)   | 10.5   |
| L1 (mm)  | 31.5   |
| M (mm)   | 16.0   |
| M1 (mm)  | 10.5   |
| N (mm)   | 63.5   |
| N1 (mm)  | 78.5   |
| Ø O (mm) | 62     |
| P        | M16    |
| Q        | G3/8   |

|           |       |
|-----------|-------|
| R (mm)    | 77.0  |
| R1 (mm)   | -     |
| R2 (mm)   | 77    |
| SW (mm)   | 22    |
| T (mm)    | 4.0   |
| U (mm)    | -     |
| V (mm)    | 55.00 |
| AA (mm)   | 15    |
| BB (mm)   | 10.0  |
| Ø CC (mm) | 16.5  |
| Ø DD (mm) | 11.0  |
| EE (mm)   | 17.0  |
| FF        | M8    |
| LL (mm)   | 77.0  |
| MM (mm)   | 100.0 |
| NN (mm)   | 100   |
| RR (mm)   | 77.0  |
| VV (mm)   | -     |
| Z (mm)    | 16.5  |