

## Cylinders ISO 1552 - Series 63

Product code: 63MT6C040A0100

Datasheet creation date: 09/03/2025 20:58

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	63
<b>Version</b>	M = standard, magnetic
<b>Costrction</b>	T = round tube
<b>Operation</b>	6 = double acting through rod
<b>Cushioning</b>	C = cushioning on both sides
<b>Bore (mm)</b>	40
<b>Construction</b>	A = standard with lock nut for rod
<b>Stroke type</b>	= standard
<b>X1 ( stroke cylinders) it has to be smaller of X2 (mm)</b>	100
<b>X2 ( stroke cylinders) it has to be greater of X1 (mm)</b>	0
<b>Temperature Range</b>	= standard (-20°/+80°C)
<b>Resistence to corrosion</b>	= standard
<b>Rod variants</b>	= standard (male thread rod)
<b>End caps variants</b>	= standard
<b>Variants of rod seals</b>	= standard
<b>Rod seal protection variants</b>	= standard
<b>Bellow protection variants</b>	= standard
<b>Rod length (mm)</b>	0
<b>Other</b>	= standard
<b>Certifications</b>	= standard

## Cylinders ISO 15552 - Series 63

Product code: 63MT6C040A0100



### DIMENSIONS

<b>MM (mm)</b>	16
<b>KK</b>	M12x1,25
<b>B (mm)</b>	35
<b>PL (mm)</b>	19.0
<b>L1 (mm)</b>	21
<b>AM (mm)</b>	24
<b>VA (mm)</b>	-
<b>EE</b>	G1/4
<b>WH (mm)</b>	30.000
<b>L2 (mm)</b>	105.0
<b>L3 (mm)</b>	5.5
<b>L4 (mm)</b>	23.0
<b>ZM (mm)</b>	165
<b>ZJ (mm)</b>	-
<b>VD (mm)</b>	5
<b>N (mm)</b>	30.0
<b>BG (mm)</b>	16.0
<b>RT</b>	M6
<b>G (mm)</b>	5.0
<b>TG (mm)</b>	38.0
<b>E (mm)</b>	55.0
<b>SW1 (mm)</b>	13
<b>SW2 (mm)</b>	6

<b>SW3 (mm)</b>	2
<b>SW4 (mm)</b>	19
<b>Cushion stroke (mm)</b>	22
<b>DE (mm)</b>	61
<b>P (mm)</b>	26
<b>R</b>	M5
<b>LB (mm)</b>	36.6
<b>D1 (mm)</b>	35.0
<b>D2 (mm)</b>	40
<b>D3 (mm)</b>	28
<b>A (mm)</b>	38.0
<b>G2</b>	G1/8
<b>H (mm)</b>	30.0
<b>H1 (mm)</b>	53.0
<b>L1B (mm)</b>	65
<b>L2B (mm)</b>	55
<b>L3B (mm)</b>	10
<b>L4B (mm)</b>	8
<b>L5B (mm)</b>	13
<b>L6B (mm)</b>	22.5
<b>L7B (mm)</b>	38.0
<b>L8B (mm)</b>	50
<b>L9B (mm)</b>	105