

## Cylinders ISO 15552 - Series 63

Product code: 63VT2C040A0100

Datasheet creation date: 09/03/2025 20:59

Check the most updated document online [click here](#)



### TECHNICAL DATA

|   |   |
|---|---|
| <b>Series</b>   | 63  |
| <b>Version</b>  | V = smooth movement (no stick slip), magnetic |
| <b>Costrction</b>   | T = round tube                                |
| <b>Operation</b>  | 2 = double effect                             |
| <b>Cushioning</b>   | C = cushioning on both sides                  |
| <b>Bore (mm)</b>  | 40  |
| <b>Construction</b>   | A = standard with lock nut for rod            |
| <b>Stroke type</b>  | = standard                                    |
| <b>X1 ( stroke cylinders) it has to be smaller of X2 (mm)</b> | 100   |
| <b>X2 ( stroke cylinders) it has to be greater of X1 (mm)</b> | 0   |
| <b>Temperature Range</b>                                      | = standard (-20°/+80°C)                       |
| <b>Resistance to corrosion</b>                                | = standard                                    |
| <b>Rod variants</b>   | = standard (male thread rod)                  |
| <b>End caps variants</b>                                      | = standard                                    |
| <b>Variants of rod seals</b>                                  | = standard                                    |
| <b>Rod seal protection variants</b>                           | = standard                                    |
| <b>Bellow protection variants</b>                             | = standard                                    |
| <b>Rod length (mm)</b>  | 0   |
| <b>Other</b>  | = standard                                    |
| <b>Certifications</b>   | = standard                                    |

## Cylinders ISO 15552 - Series 63

Product code: 63VT2C040A0100



### DIMENSIONS

|          |          |
|----------|----------|
| MM (mm)  | 16       |
| KK       | M12x1,25 |
| B (mm)   | 35       |
| PL (mm)  | 19.0     |
| L1 (mm)  | 21       |
| AM (mm)  | 24       |
| VA (mm)  | 4        |
| EE       | G1/4     |
| WH (mm)  | 30.000   |
| L2 (mm)  | 105.0    |
| L3 (mm)  | 5.5      |
| L4 (mm)  | 23.0     |
| ZM (mm)  | -        |
| ZJ (mm)  | 135      |
| VD (mm)  | 5        |
| N (mm)   | 30.0     |
| BG (mm)  | 16.0     |
| RT       | M6       |
| G (mm)   | 5.0      |
| TG (mm)  | 38.0     |
| E (mm)   | 55.0     |
| SW1 (mm) | 13       |
| SW2 (mm) | 6        |

|                     |      |
|---------------------|------|
| SW3 (mm)            | 2    |
| SW4 (mm)            | 19   |
| Cushion stroke (mm) | 22   |
| DE (mm)             | 61   |
| P (mm)              | 26   |
| R                   | M5   |
| LB (mm)             | 36.6 |
| D1 (mm)             | 35.0 |
| D2 (mm)             | 40   |
| D3 (mm)             | 28   |
| A (mm)              | 38.0 |
| G2                  | G1/8 |
| H (mm)              | 30.0 |
| H1 (mm)             | 53.0 |
| L1B (mm)            | 65   |
| L2B (mm)            | 55   |
| L3B (mm)            | 10   |
| L4B (mm)            | 8    |
| L5B (mm)            | 13   |
| L6B (mm)            | 22.5 |
| L7B (mm)            | 38.0 |
| L8B (mm)            | 50   |
| L9B (mm)            | 105  |