

Electromechanical cylinders - Series 6E

Product code: 6E100BS0400P20AP

Datasheet creation date: 07/03/2025 17:01

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|----------------------------|--------------------------|
| Series | 6E |
| Size (mm) | 100 |
| Transmission | BS = ball screw |
| Stroke (mm) | 400 |
| Screw pitch (mm) | P20= 20mm |
| Construction | A= standard with rod nut |
| Extended piston rod | 0 |
| Version | P = IP65 |
| Motor connection | cylinder only |
| Motor | |
| Brake | |
| Encoder | |

Electromechanical cylinders - Series 6E

Product code: 6E100BS0400P20AP



DIMENSIONS

| | |
|----------|-----------|
| AM (mm) | 40 |
| B (mm) | 65 |
| BG (mm) | 18 |
| E (mm) | 115.0 |
| F (mm) | 24 |
| F1 (mm) | 13.0 |
| F2 (mm) | 18 |
| F3 (mm) | 62 |
| KK (mm) | M20 x 1,5 |
| (mm) | 20 |
| L1 (mm) | 38 |
| L2 (mm) | 232 |
| L3 (mm) | 0.0 |
| MM (mm) | 50 |
| N (mm) | 44 |
| R (mm) | 40.0 |
| RT (mm) | M10 |
| PL (mm) | 42 |
| SW1 (mm) | 22 |
| SW2 | G 1/4 |
| SW3 (mm) | 30 |
| TG (mm) | 89.0 |
| VA (mm) | 8 |

| | |
|---------|-------|
| VD (mm) | 8 |
| Y | M6 |
| Y1 (mm) | 10 |
| Y2 (mm) | 3 |
| Y3 (mm) | 16 |
| WH (mm) | 51 |
| ZJ (mm) | 283.0 |