



**DECLARATION
CE
OF COMPLIANCE**

Code
86-3720-0013 Rev.A

Page 1 of 3



The undersigned, representative of the following manufacturer

Camozzi SPA

Via Eritrea, 20/I
25126 Brescia – Italy
Tel: +39 030 37921
Fax: +39 030 2400464
E-mail: info@camozzi.com
<http://www.camozzi.com>

Herewith declares that the product :

SOLENOID SERIES B

with the present versions at page 3

Result to be in conformity with the provisions of the following European Community's directives:

2004/108/EC	DIRECTIVE 2004/108/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL OF 15 DECEMBER 2004 ON THE APPROXIMATION OF THE LAWS OF THE MEMBERS STATES RELATING TO ELECTROMAGNETIC COMPATIBILITY AND REPEALING DIRECTIVE 89/336/EEC
2006/95/EC * where applicable	DIRECTIVE 2006/95/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL OF 12 DECEMBER 2006 ON THE HARMONISATION OF THE LAWS OF MEMBER STATES RELATING TO ELECTRICAL EQUIPMENT DESIGNED FOR USE WITHIN CERTAIN VOLTAGE LIMITS

and that all standards and/or technical specifications have been applied are indicated on page 2:

Brescia, 31/03/2015

Camozzi SPA
Product Manager
Fabio Bottarelli



**DECLARATION
CE
OF COMPLIANCE**

Code
86-3720-0013 Rev.A

Page 2 of 3

Reference relative to the standards and/or technical specifications, or parts of these, used for the present declaration of compliance:

Harmonised Standards:

Number : Year	Title
EN 60730-1:2011	Automatic electrical controls for household and similar use -- Part 1: General requirements



DECLARATION CE OF COMPLIANCE

Code
86-3720-0013 Rev.A

Page 3 of 3

B Series Solenoids – Item features

Model	Solenoid measure	Voltage	Power	Overmolding material	T _A	Insulation class
B7B	22 mm	24 VAC 50/60HZ	9 VA	PA MXD6	80°C	H
B7H		24 VAC 50/60HZ	4 VA		80°C	H
B7D*		110 V AC 50/60HZ	9 VA		80°C	H
B7E*		230 VAC 50/60HZ	9 VA		80°C	H
B72		12 VDC	10 W		80°C	H
B73		24 VDC	10 W		80°C	H
B74		24 VDC	7 W		80°C	H
B8B	30 mm	24 VAC 50HZ	15 VA		120°C	H
B8D*		110 V AC 50/60HZ	15 VA		120°C	H
B8E*		220/230 VAC 50/60HZ	15 VA		120°C	H
B8F*		220/230 VAC 50/60HZ	21 VA		80°C	H
B82		12 VDC	19 W		120°C	H
B83		24 VDC	19 W		120°C	H
B8BK	30 mm for NO	24 VAC 50HZ	15 VA		120°C	H
B8DK*		110 V AC 50HZ	15 VA	120°C	H	
B8EK*		220/230 VAC 50HZ	15 VA	120°C	H	
B8FK*		220/230 VAC 50/60HZ	21 VA	80°C	H	
B82K		12 VDC	19 W	120°C	H	
B83K		24 VDC	19 W	120°C	H	
B9B	36 mm	24 VAC 50HZ	29 VA	120°C	H	
B9D*		110 V AC 50/60HZ	29 VA	120°C	H	
B9E*		220/230 VAC 50HZ	29 VA	120°C	H	
B92		12 VDC	30 W	120°C	H	
B93		24 VDC	30 W	120°C	H	