



# EU Declaration of Conformity

Code: 5000006530

Version -

Rev. : --

Page 1 of 3



The undersigned, representative of the following manufacturer

**Camozzi spa**

Via Eritrea, 20/I  
25126 Brescia – Italy  
Tel: +39 030 37921  
Fax: +39 030 2400464  
E-mail: [info@camozzi.com](mailto:info@camozzi.com)  
<http://www.camozzi.com>

herewith declares that the products:

**Series PG digital pressure gauges**

(For more details, and certified codes see page 3)

**Result to be in conformity with the provisions of the following European Community's directive:**

**2014/30/EU**

Directive 2014/30/EU of the European Parliament and of the Council of 26 February 2014 on the harmonisation of the laws of the Member States relating to electromagnetic compatibility (recast) Text with EEA relevance

and that all the standards and/or technical specifications indicated on page 2 are applied.

Brescia, 02/11/2017

Camozzi SPA

Product Certification Manager

Fabrizio Guerrini



## EU Declaration of Conformity

Code: 5000006530

Version -

Rev. : --

Page 2 of 3

**Reference relative to the standards and/or technical specifications, or parts of them, used for the present declaration of conformity:**

**Harmonised standards:**

Nr. Year	Title
EN 61000-6-1: 2007	Electromagnetic compatibility (EMC) — Part 6-1: Generic standards — Immunity for residential, commercial and light-industrial environments
EN 61000-6-3: 2007 + A1:2011	Electromagnetic compatibility (EMC) — Part 6-3: Generic standards — Emission standard for residential, commercial and light-industrial environments



# EU Declaration of Conformity

Code: 5000006530

Version -

Rev. : --

Page 3 of 3

## Series PG digital pressure gauges coding example

<b>PG</b>	<b>010</b>	<b>-</b>	<b>P</b>	<b>B</b>	<b>-</b>	<b>1/8</b>	<b>-</b>	<b>2</b>
-----------	------------	----------	----------	----------	----------	------------	----------	----------

PG	SERIES	PG
010	BOTTOM SCALE:	010 = 10 bar 001 = -1 bar
P	PRESSURE RANGE:	P = pressure V = vacuum
B	LIGHTING:	B = back light
1/8	PNEUMATIC CONNECTIONS:	1/8 = G 1/8 BSPP; M5 1/4 = G 1/4 BSPP; M5 (for battery-powered version only)
2	ELECTRICAL CONNECTION (for version with cable only):	2 = with unshielded 2-pole cable of 2 m M = with cable of 150 mm and M8 4-pole connector