

Stainless steel Cylinders (DIN/ISO 6431 - Series 90)

Product code: 90M2A080A0780

Datasheet creation date: 07/03/2025 17:23

Check the most updated document online [click here](#)




TECHNICAL DATA

| | |
|------------------------|--|
| Series | 90 |
| Diameter (mm) | 80 |
| Version | M = standard magnetic |
| Operation | 2 = double-acting (front and rear cush.) |
| Materials | A = stainless steel AISI 316 (SS 2343), joints NBR |
| Construction | A = standard |
| Stroke type | variable |
| Stroke (mm) | 780 |
| rod seals viton | - |

Stainless steel Cylinders (DIN/ISO 6431 - Series 90)

Product code: 90M2A080A0780



DIMENSIONS

| | |
|----------------|---------|
| A (mm) | 40 |
| B (mm) | 45 |
| BG (mm) | 16 |
| BF (mm) | 15 |
| E (mm) | 95 |
| EE | G3\8 |
| G (mm) | 36.0 |
| KK | M20x1,5 |
| L (mm) | 128 |
| MM (mm) | 25 |
| N (mm) | 8.5 |
| PL (mm) | 23 |
| RT (mm) | M10 |
| R1 (mm) | 92 |
| R2 (mm) | 34 |
| SW (mm) | 21 |
| T (mm) | M10 |
| TG (mm) | 72.0 |
| VA (mm) | 4 |
| VD (mm) | 34 |
| WH (mm) | 46 |
| ZM (mm) | 220 |