

## Quick exhaust 3/2 way safety valves - Series MD Safemax

Product code: MD1-V1640B

Datasheet creation date: 20/05/2026 08:25

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series (mm)</b>	MD
<b>Size</b>	1 = 42 mm
<b>Component</b>	V = 3/2 NC solenoid valve
<b>DESIGN TYPE</b>	16 = internal servo pilot
<b>Channel</b>	4 = double
<b>Accessories</b>	0 =without silencer
<b>Sensor</b>	B = CE sensor cable L 5mt
	= without fittings
<b>Fixing</b>	= without fixing accessories

## Quick exhaust 3/2 way safety valves - Series MD Safemax

Product code: MD1-V1640B

### **■** DIMENSIONS

<b>A</b>	-
<b>B</b>	G 1/8
<b>C (mm)</b>	84
<b>D</b>	Ø30
<b>E (mm)</b>	84
<b>G</b>	G1/8
<b>I (mm)</b>	43
<b>L (mm)</b>	Ø4
<b>M (mm)</b>	9.5
<b>N (mm)</b>	119.4
<b>O (mm)</b>	26.2
<b>R (mm)</b>	51.7
<b>S (mm)</b>	35.1
<b>T (mm)</b>	34.6
<b>V (mm)</b>	9
<b>X (mm)</b>	141
<b>Z (mm)</b>	50
<b>W (mm)</b>	63
<b>Weight (kg)</b>	0.6