

Cylinders with integrated guide - Series QCT QCB

Product code: QCB2A040A150

Datasheet creation date: 09/03/2025 23:10

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|----------------------|--|
| Series | QC |
| Version | B = linear ball bearings |
| Operation | 2 = double acting |
| Materials | A = anodized aluminium body rolled stainless steel 303 piston rod hardened steel C50 columns for QCB |
| Diameter (mm) | 40 |
| Construction | A = standard |
| Stroke type | standard |
| Stroke (mm) | 150 |

Cylinders with integrated guide - Series QCT QCB

Product code: QCB2A040A150



DIMENSIONS

| | |
|----------------|-------|
| L3 (mm) | 110.0 |
| C (mm) | 16 |
| B (mm) | 44.0 |
| O2 (mm) | 124 |
| O4 (mm) | 84 |
| A (mm) | 12 |
| D (mm) | 16 |
| E1 (mm) | 104 |
| E2 (mm) | 30 |
| F | G 1/8 |
| F1 (mm) | 13.0 |
| F2 (mm) | 12.0 |
| F3 (mm) | 38.0 |
| F4 (mm) | 13.0 |
| F5 (mm) | 18.0 |
| F6 (mm) | 13.0 |
| G1 (mm) | 118 |
| G2 (mm) | 45 |
| H (mm) | 106 |
| H1 (mm) | 86 |
| L1 (mm) | 44.0 |
| L2 (mm) | 66.0 |
| M1 (mm) | 120 |

| | |
|-------------------|---------|
| M2 (mm) | 54 |
| N (mm) | 40 |
| O1 (mm) | 22 |
| O3 (mm) | 50 |
| P1 | M8x1.25 |
| P2 | M8x1.25 |
| P3 | M8x1.25 |
| Q (mm) | 20 |
| R (mm) | 16 |
| heavy (mm) | 10 |
| Y (mm) | 50 |
| Y1 (mm) | 4 |
| Y2 (mm) | 4.5 |
| Y3 (mm) | 3 |
| Y4 (mm) | 6 |
| X (mm) | 6.5 |
| X1 (mm) | 11 |
| X2 (mm) | 6.5 |
| J (mm) | 72 |
| K | M6 |