

## Short stroke magnetic cylinders - Series QP-QPR

Product code: QP3A100A150

Datasheet creation date: 09/03/2025 23:41

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                        |                             |
|------------------------|-----------------------------|
| <b>Series</b>          | QP = standard               |
| <b>Diameter (mm)</b>   | 100                         |
| <b>Operation</b>       | 3=double-acting through rod |
| <b>Materials</b>       | A = rolled stainless steel  |
| <b>Construction</b>    | A = standard                |
| <b>Stroke type</b>     | = variable                  |
| <b>Stroke (mm)</b>     | 150                         |
| <b>Atex</b>            | No Atex                     |
| <b>Rod lenght (mm)</b> | 0                           |

## Short stroke magnetic cylinders - Series QP-QPR

Product code: QP3A100A150



### DIMENSIONS

|                 |        |
|-----------------|--------|
| <b>A (mm)</b>   | 117.0  |
| <b>B (mm)</b>   | -      |
| <b>B1 (mm)</b>  | -      |
| <b>B2 (mm)</b>  | 94     |
| <b>Ø C (mm)</b> | 25     |
| <b>D (mm)</b>   | 123.50 |
| <b>E (mm)</b>   | 117.00 |
| <b>G (mm)</b>   | 68.5   |
| <b>G1 (mm)</b>  | 0      |
| <b>H1 (mm)</b>  | 20.3   |
| <b>H (mm)</b>   | 20.3   |
| <b>J (mm)</b>   | 10.5   |
| <b>J1</b>       | M12    |
| <b>K (mm)</b>   | 17.0   |
| <b>L (mm)</b>   | 10.5   |
| <b>L1 (mm)</b>  | 31.5   |
| <b>M (mm)</b>   | 15.0   |
| <b>M1 (mm)</b>  | 10.5   |
| <b>N (mm)</b>   | 80.5   |
| <b>N1 (mm)</b>  | -      |
| <b>Ø O (mm)</b> | 80     |
| <b>P</b>        | M16    |
| <b>Q</b>        | G3/8   |

|                  |       |
|------------------|-------|
| <b>R (mm)</b>    | -     |
| <b>R1 (mm)</b>   | -     |
| <b>R2 (mm)</b>   | 94    |
| <b>SW (mm)</b>   | 22    |
| <b>T (mm)</b>    | 4.0   |
| <b>U (mm)</b>    | -     |
| <b>V (mm)</b>    | 65.00 |
| <b>AA (mm)</b>   | 15    |
| <b>BB (mm)</b>   | 10.0  |
| <b>Ø CC (mm)</b> | 16.5  |
| <b>Ø DD (mm)</b> | 11.0  |
| <b>EE (mm)</b>   | 17.0  |
| <b>FF</b>        | M8    |
| <b>LL (mm)</b>   | 94.0  |
| <b>MM (mm)</b>   | 115.0 |
| <b>NN (mm)</b>   | 115   |
| <b>RR (mm)</b>   | 94.0  |
| <b>VV (mm)</b>   | -     |
| <b>Z (mm)</b>    | 16.5  |