

Short stroke magnetic cylinders - Series QP-QPR

Product code: QPR2A080A075

Datasheet creation date: 09/03/2025 23:38

Check the most updated document online [click here](#)




TECHNICAL DATA

Series	QPR = anti-rotation
Diameter (mm)	80
Operation	2=double-acting
Materials	A = rolled stainless steel
Construction	A = standard
Stroke type	N = standard
Stroke (mm)	75
Atex	No Atex
Rod lenght (mm)	0

Short stroke magnetic cylinders - Series QP-QPR

Product code: QPR2A080A075



DIMENSIONS

A (mm)	98.0
B (mm)	77.0
B1 (mm)	-
B2 (mm)	77
Ø C (mm)	25
D (mm)	104.00
E (mm)	98.00
G (mm)	57.5
G1 (mm)	-
H1 (mm)	16.2
H (mm)	16.2
J (mm)	M12
J1	M12
K (mm)	17.0
L (mm)	10.5
L1 (mm)	31.5
M (mm)	16.0
M1 (mm)	10.5
N (mm)	63.5
N1 (mm)	78.5
Ø O (mm)	62
P	M16
Q	G3/8

R (mm)	77.0
R1 (mm)	-
R2 (mm)	77
SW (mm)	22
T (mm)	4.0
U (mm)	-
V (mm)	55.00
AA (mm)	15
BB (mm)	10.0
Ø CC (mm)	16.5
Ø DD (mm)	11.0
EE (mm)	17.0
FF	M8
LL (mm)	77.0
MM (mm)	100.0
NN (mm)	100
RR (mm)	77.0
VV (mm)	-
Z (mm)	16.5