

## Short stroke magnetic cylinders - Series QP-QPR

Product code: QPR3A050A100

Datasheet creation date: 09/03/2025 23:37

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	QPR = anti-rotation
<b>Diameter (mm)</b>	50
<b>Operation</b>	3=double-acting through rod
<b>Materials</b>	A = rolled stainless steel
<b>Construction</b>	A = standard
<b>Stroke type</b>	N = standard
<b>Stroke (mm)</b>	100
<b>Atex</b>	No Atex
<b>Rod lenght (mm)</b>	0

## Short stroke magnetic cylinders - Series QP-QPR

Product code: QPR3A050A100



### DIMENSIONS

<b>A (mm)</b>	64.0
<b>B (mm)</b>	50.0
<b>B1 (mm)</b>	-
<b>B2 (mm)</b>	50
<b>Ø C (mm)</b>	16
<b>D (mm)</b>	72.00
<b>E (mm)</b>	64.00
<b>G (mm)</b>	42.2
<b>G1 (mm)</b>	-
<b>H1 (mm)</b>	11.2
<b>H (mm)</b>	11.2
<b>J (mm)</b>	M8
<b>J1</b>	M8
<b>K (mm)</b>	10.5
<b>L (mm)</b>	6.0
<b>L1 (mm)</b>	21.0
<b>M (mm)</b>	13.0
<b>M1 (mm)</b>	9.0
<b>N (mm)</b>	54.8
<b>N1 (mm)</b>	66.8
<b>Ø O (mm)</b>	37.5
<b>P</b>	M8
<b>Q</b>	G1/4

<b>R (mm)</b>	50.0
<b>R1 (mm)</b>	-
<b>R2 (mm)</b>	50
<b>SW (mm)</b>	13
<b>T (mm)</b>	3.5
<b>U (mm)</b>	-
<b>V (mm)</b>	40.00
<b>AA (mm)</b>	12
<b>BB (mm)</b>	6.8
<b>Ø CC (mm)</b>	10.5
<b>Ø DD (mm)</b>	6.5
<b>EE (mm)</b>	10.0
<b>FF</b>	M6
<b>LL (mm)</b>	50.0
<b>MM (mm)</b>	65.0
<b>NN (mm)</b>	65
<b>RR (mm)</b>	50.0
<b>VV (mm)</b>	-
<b>Z (mm)</b>	8.5