

Series QX - Twin Cylinders

Product code: QXB2A020A075

Datasheet creation date: 10/03/2025 00:13

Check the most updated document online [click here](#)



TECHNICAL DATA

Series (mm)	QX
Version (mm)	B = linear ball bearings
Operation (mm)	2 = double-acting (1 flange) radial pressure supply
Materials (mm)	A = anodized aluminium body, rolled stainless steel 303 piston rod
Diameter (mm)	20
Construction (mm)	A = standard
Stroke cylinder (mm)	75

Series QX - Twin Cylinders

Product code: QXB2A020A075



DIMENSIONS

A (mm)	62
B (mm)	25
C (mm)	60
E (mm)	22
F (mm)	50
G (mm)	6
I (mm)	4.5
M (mm)	12
Q (mm)	16
R (mm)	18
L1 (mm)	67.5
L2 (mm)	84.0
L3 (mm)	39.5
L4 (mm)	9.0
L5 (mm)	25
L6 (mm)	60.0
L7 (mm)	20
L8 (mm)	30
L9 (mm)	60.0
L10 (mm)	31.0
L11 (mm)	57.2
H2 (mm)	5.5
H3 (mm)	4.0

H4 (mm)	4.5
H5 (mm)	6.0
H6 (mm)	8
H7 (mm)	4
H8 (mm)	0.0
H10 (mm)	10.5
H11 (mm)	20.2
H12 (mm)	8.0
H13 (mm)	9
H14 (mm)	12.5
D1	M6
D2 (mm)	9.5
D3 (mm)	4.0
D4 (mm)	M4
D5	M4
D6	M4
D7 (mm)	4.0
D8 (mm)	0
D9 (mm)	0.0
D10	M5
NN (mm)	10
EE	M5
J (mm)	0.0