

## Stopper cylinders - Series ST

Product code: ST324R020F015

Datasheet creation date: 10/03/2025 00:15

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	ST32
<b>Operation</b>	4=single-acting rear spring
<b>Design</b>	R = anti-rotation
<b>Diameter (mm)</b>	20
<b>Construction</b>	F = female rod thread
<b>Stroke (mm)</b>	15

## Stopper cylinders - Series ST

Product code: ST324R020F015

### **■** DIMENSIONS

<b>AF (mm)</b>	6.0
<b>BG (mm)</b>	20.0
<b>G (mm)</b>	10.9
<b>H1 (mm)</b>	0.0
<b>D (mm)</b>	12
<b>D1 (mm)</b>	25
<b>D2 (mm)</b>	0
<b>D3 (mm)</b>	0
<b>D4 (mm)</b>	9
<b>D5 (mm)</b>	5
<b>D6 (mm)</b>	9
<b>D7</b>	4
<b>E (mm)</b>	35.8
<b>EE</b>	M5
<b>E1 (mm)</b>	0
<b>KF (mm)</b>	3
<b>LA (mm)</b>	5
<b>PL (mm)</b>	6.5
<b>RT</b>	M5
<b>T1 (mm)</b>	0
<b>T2 (mm)</b>	2.5
<b>TG (mm)</b>	22.0
<b>L (mm)</b>	35.8

<b>ZA (mm)</b>	53.5
<b>ZB (mm)</b>	64.0
<b>L1 (mm)</b>	9.5
<b>L2 (mm)</b>	68.0
<b>L3 (mm)</b>	71
<b>L4 (mm)</b>	73
<b>R (mm)</b>	10
<b>P (mm)</b>	2.0
<b>B1 (mm)</b>	4
<b>SW1 (mm)</b>	10.0
<b>T3 (mm)</b>	1.2