



EU declaration of conformity

DOCUMENT Nr.5000063911

VER. -

REV. --

Pag. 1 of 3



The undersigned, representative of the following manufacturer

Camozzi Automation S.p.A.

Via Eritrea, 20/I
25126 Brescia - Italy
Tel: +39 030 37921
Fax: +39 030 2400464
E-mail: info@camozzi.com
<http://www.camozzi.com>

herewith declares that the products:

MAGNETIC PROXIMITY SWITCHES
Series CSG

The object of the declaration described above is in conformity with the relevant Union harmonisation legislation:

2014/30/EU	DIRECTIVE 2014/30/EU OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 26 February 2014 on the harmonisation of the laws of the Member States relating to electromagnetic compatibility
-------------------	--

and that all the standards and/or technical specifications indicated on page 2 are applied.

This declaration of conformity is issued under the sole responsibility of the manufacturer

Brescia Italy 04/09/2023

Camozzi Automation S.P.A.

Product Certification Manager

Fabrizio Guerrini

Declaration in accordance with ISO / IEC 17050-1

	EU declaration of conformity	DOCUMENT Nr.5000063911	
		VER. -	REV. --
		Pag. 2 of 3	

Reference relative to the standards and/or technical specifications, or parts of them, used for the present declaration of compliance

Reference Number	Date of issue	Title
EN 61000-6-2	2005	Electromagnetic compatibility (EMC) – Part 6-2: Generic standards - Immunity for industrial environments
EN 61000-6-2/AC	2005	
EN 61000-6-4	2007	Electromagnetic compatibility (EMC) – Part 6-4: Generic standards - Emission standard for industrial environments
EN 61000-6-4/A1	2011	

	EU declaration of conformity	DOCUMENT Nr.5000063911	
		VER. -	REV. --
		Pag. 3 of 3	

Code Sample:

CS	G	-	2	2	3	-	2	-	UL
----	---	---	---	---	---	---	---	---	----

CS	Series
G	SLOT TYPE G = T slot
2	OPERATION 2 = Reed Normally Open 3 = Magnetoresistive PNP 5 = Magnetoresistive NPN 6 = Magnetoresistive PNP Normally Closed 7 = Magnetoresistive NPN Normally Closed
2	CONNECTIONS 2 = 2 wires 3 = 3 wires
3	POWER SUPPLY VOLTAGE 3 = 5/10 ÷ 30 V AC/DC (PNP) 4 = 10 ÷ 28 V DC (PNP)
2	Cable length (for CSH only): 2 = 2m 5 = 5m 10 = 10 m
UL	CERTIFICATION: = No certification EX = ATEX certification UL = UL certification