



EU declaration of conformity

86-3720-0006 Rev. E

Pag. 1 of 3



The undersigned, representative of the following manufacturer

Camozzi spa

Via Eritrea, 20/I
25126 Brescia – Italy
Tel: +39 030 37921
Fax: +39 030 2400464
E-mail: info@camozzi.com
<http://www.camozzi.com>

herewith declares that the products:

**MAGNETIC PROXIMITY SWITCHES
Series CST – CST – CSH**

The object of the declaration described above is in conformity with the relevant Union harmonisation legislation:

2014/30/EU	DIRECTIVE 2014/30/EU OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 26 February 2014 on the harmonisation of the laws of the Member States relating to electromagnetic compatibility
2014/35/EU * * where applicable	DIRECTIVE 2014/35/EU OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 26 February 2014 on the harmonisation of the laws of the Member States relating to the making available on the market of electrical equipment designed for use within certain voltage limits and that all the standards

and that all the standards and/or technical specifications indicated on page 2 are applied.

This declaration of conformity is issued under the sole responsibility of the manufacturer

Brescia Italy 19/10/2016

CAMOZZI SPA

Fabrizio Guerrini

Product Certification Manager

Declaration in accordance with ISO / IEC 17050-1



EU declaration of conformity

86-3720-0006 Rev. E

Pag. 2 of 3

Reference relative to the standards and/or technical specifications, or parts of them, used for the present declaration of compliance

Reference Number	Date of issue	Title
EN 60947-1	2007	Low-voltage switchgear and controlgear - Part 1: General rules
EN 60947-5-2	2007	Low-voltage switchgear and controlgear - Part 5-2: Control circuit devices and switching elements - Proximity switches
EN 60529	1991	Degrees of protection provided by enclosures (IP Code)
+A1	2000	
+A2	2013	



EU declaration of conformity

86-3720-0006 Rev. E

Pag. 1 di 3

Code Sample:

CS	T	-	2	2	0	N	-	5
----	---	---	---	---	---	---	---	---

CS	Series
T	SLOT TYPE T = T slot V = Vslot H = inserting slot from the top
2	OPERATION 2 = Reed NO 3 = magnetoresistive 4 = Reed NC 5 = Hall-effect sensor
2	CONNECTIONS 2 = 2 wires (Reed only) 3 = 3 wires 5 = 2 wires with M8 connector (Reed only) 6 = 3 wires with M8 connector
0	POWER SUPPLY VOLTAGE 0 = 10-110V DC; 10-230V AC (PNP) 1 = 30-110V DC; 30-230V AC (PNP) 2 = 3 wires cst (PNP) 3 = 10-30V AC/DC (PNP) 4 = 10-27V DC (PNP)
N	Note N= Connection in conformity with standard EN 60947-5-2 (CST/CSV-250N only)
5	Cable length (for CSH only): 2= 2m 5= 5m