
# Series 3 Plug-In valve islands, Multipole and Fieldbus

Plug-In system for Series 3 solenoid valves, G1/8 port. Valve functions: 2x3/2, 5/2 and 5/3-way CO CC CP. Multipole with a 25-pin Sub-D connector. It can interface with all major serial communication protocols.



The Multipole version of Series 3 Plug-In valve island can be easily installed thanks to the front position of the Sub-D connector. The accessories of the new connection system to the Series CX serial nets enable to handle up a multipole valve island by means of a Sub-D connector or through a node integrated in the island.

- » Flexible assembly through monostable and bistable 2- and 3-position modules
- » Electrical connection and front pneumatic outputs
- » Available protocols: PROFIBUS-DP, DeviceNet, CANopen, EtherNet/IP, EtherCAT, PROFINET

The electric and pneumatic modules have 2- and 3-position modularity. To optimize the signals distribution, electric modules are available for monostable and bistable valves. The pneumatic modularity enables the creation of zones with differentiated pressure.


Manuals, instruction sheets and configuration files can be found on catalogue.camozzi.com or on the QR code on the lable of the product.

The modularity of the electric and pneumatic parts allows to install up to a maximum of 22 solenoids on 22 valve positions.

# **GENERAL DATA**

PNEUMATIC SECTION	
Valve construction	spool type with seals
Valve functions	5/2 - 5/3 CC - 5/3 CO - 5/3 CP - 2x3/2 NO - 2x3/2 NC - 1 3/2 NO + 1 3/2 NC
Materials	AL body, stainless steel spool, NBR seals, technopolymer
Mounting	through-out holes in the manifold
Ports	valve = G1/8 - manifold = G3/8
Installation	in any position
Operating temperature	from 0°C to 60°C (with dry air at -20°C)
Nominal flow rate	Qn 700 Nl/min
Nominal diameter	7 mm
Fluid	Filtered air, class 7.4.4 according to ISO 8573-1-2010, without lubrication. If lubricated air is used, it is recommended to use ISO VG32 oil, and to never interrupt the lubrication.
<b>ELECTRICAL SECTION - MULTIPOLE VERSION</b>	
Max absorption	3 A
Type of connection	Multipole 25-pin male Sub-D
Supply voltage	24 V DC +/- 10%
Max number of solenoids	22 on 22 valve positions
Signalling	yellow LED
Duty cycle	ED 100%
Protection class	IP65
ELECTRICAL SECTION - FIELDBUS VERSION	
General characteristics	see the section about the Series CX multi-serial module (2.3.50)
Max absorption	digital outputs/analogic inputs and outputs 3A digital/analogic inputs 3 A
Voltage tolerances	logic supply 24 V DC +/- 10% power supply 24 V DC +/- 10%


#### MULTIPOLE VERSION AND MULTIPOLE WITH SUB-D ADAPTER





In the Multipole version the front position of the 25 pin Sub-D connector makes the connection easier. The connectors with prewired cable, which are available in different lengths and with axial or radial orientation, simplify the electrical connection. The Island can be configured up to a max. of 22 solenoids, using monostable and bistable electrical modules, on 22 valve positions, for example 22 monostable solenoid valves. Thanks to the 2- or 3-position pneumatic modularity, diaphragms and plates of supplementary supply, it is possible to create zones with differentiated pressure. The Multipole version of Series 3 valve island can be connected by means of a Sub-D adapter. In this way a standard Multipole Island can be inserted as expansion in the subnet of the Fieldbus version.

#### VERSIONS: FIELDBUS WITH CPU MODULE AND EXPANSION FIELDBUS



The Individual Fieldbus version of Series 3 can be interfaced through a specific module with the Series CX multi-serial module according to the different communication protocols (PROFIBUS-DP, DeviceNet, CANopen, EtherNet/IP, EtherCAT, PROFINET).

Like the Multipole one, the Fieldbus version is able to create islands with 22 coils on 22 valve positions adding a wide range of electrical modules like digital/analog inputs/outputs of 0-10 V and 4-20 mA.

It is possible to insert Initial Subnet Modules in the version with CPU module. These Modules enable to create a subnet with tree structure or in series. On the subnet you can connect Expansion Islands. These expansions have the same possibilities to use the different electric modules, like digital and analog inputs and outputs and further Initial Subnet Modules. Also with this version the same rules as the CPU module and Multipole apply.

#### **CODING EXAMPLE - MULTIPOLE VERSION**

3 P 8 - 03A	- BDACAC - 2BC3MU2BMXU2B2M - G77					
3	SERIES					
Р	TYPE: P = Plug-In					
8	SIZE: 8 = 1/8					
03A	CONNECTION: 000 = no connector/cable					
	CONNECTOR WITH CABLE AXIAL OUTPUT: 03A = 3 m 10A = 10 m 15A = 15 m 20A = 20 m 25A = 25 m CONNECTOR WITH CABLE RADIAL OUTPUT: 03R = 3 m 10R = 10 m 15R = 15 m 20R = 20 m 25R = 25 m					
	CONNECTOR WITHOUT CABLE: 4XA = 25-pin axial 4XR = 25-pin radial					
BDACAC	CONFIGURATION OF SUBBASE: A = 2 positions with bistable board B = 3 positions with bistable board C = 2 positions with monostable board D = 3 positions with monostable board					
2BC3MU2BMXU2B2M	VALVE FUNCTION: E = empty positionM = 5/2 Monostable, internal servo-pilot supply B = 5/2 Bistable, internal servo-pilot supply C = 2 x 3/2 NC, internal servo-pilot supply G = 1 x 3/2 NC, internal servo-pilot supply H = 5/3 Closed Centres, internal servo-pilot supply N = 5/3 Pressure Centres, internal servo-pilot supply N = 5/3 Pressure Centres, internal servo-pilot supply Q = 2 x 3/2 NC, external servo-pilot supply Y = 5/2 Bistable, external servo-pilot supply Q = 2 x 3/2 NC, external servo-pilot supply S = 1 x 3/2 NC, external servo-pilot supply M = 5/3 Closed Centres, external servo-pilot supply S = 1 x 3/2 NC, external servo-pilot supply S = 1 x 3/2 NC, external servo-pilot supply M = 5/3 Closed Centres, external servo-pilot supply S = 1 x 3/2 NC, external servo-pilot supply M = 5/3 Pressure Centres, external servo-pilot supply M = 5/3 Pressure Centres					
G77	SOLENOID MATERIAL: G = PA U = PET					


3P8-03R-ADCB-2B3MT2M3V-G77: valve island with 10 positions, radial connector and 3-meter cable. Bases: the first with 2 bistables positions, the second with 3 monostable pos., the third with 2 monostable pos., the fourth with 3 bistable pos. Valves: 2 bistable, 3 monostables, diafragm on channels 1,3,5, 2 monostables, 3 Closed Centres, 24 V Solenoids.



# **CODING EXAMPLE - FIELDBUS VERSION**

3 S 8 - 01 -	2AQRS - BDACAC - 2BC3MU2BMXU2B2M - G77
r	
3	SERIES
S	CONNECTION: S = Fieldbus
8	SIZE: 8 = 1/8
01	PROTOCOL: 01 = PROFIBUS-DP 02 = DeviceNet 03 = CANopen 04 = EtherNet/IP 05 = EtherCAT 06 = PROFINET 99 = Expansion Module
ZAQRS	INPUT / OUTPUT MODULES: 0 = no module A = 8 digital inputs M8 B = 4 digital inputs M8 C = 2 analog inputs 4-20 mA D = 2 analog inputs 4-20 mA + 1 input 0-10 V Q = 4 M12 duo digital outputs R = 2 analog output 4-20 mA + 1 input 0-10 V U = 1 analog output 4-20 mA + 1 output 0-10 V V = 1 analog output 4-20 mA + 1 input 0-10 V Z = 1 analog output 4-20 mA + 1 input 0-10 V Z = 1 analog output 4-20 mA + 1 input 0-10 V Y = 1 analog output 0-10 V + 1 input 0-10 V S = Initial subnet module
BDACAC	CONFIGURATION OF SUBBASE: A = 2 positions with bistable board B = 3 positions with bistable board C = 2 positions with monostable board D = 3 positions with monostable board
2BC3MU2BMXU2B2M	VALVE FUNCTION: E = empty position
	M = 5/2 Monostable, internal servo-pilot supply B = 5/2 Bistable, internal servo-pilot supply C = 2 × 3/2 NC, internal servo-pilot supply A = 2 × 3/2 NO, internal servo-pilot supply G = 1 × 3/2 NC + 1 × 3/2 NO, internal servo-pilot supply H = 5/3 Closed Centres, internal servo-pilot supply K = 5/3 Exhaust Centres, internal servo-pilot supply N = 5/3 Pressure Centres, internal servo-pilot supply D = 5/2 Monostable, external servo-pilot supply Y = 5/2 Bistable, external servo-pilot supply Q = 2 × 3/2 NC, external servo-pilot supply S = 1 × 3/2 NC + 1 × 3/2 NO, external servo-pilot supply
	V = 5/3 Closed Centres, external servo-pilot supply Z = 5/3 Exhaust Centres, external servo-pilot supply W = 5/3 Pressure Centres, external servo-pilot supply L = plate with closed free position
	X = supply plate and supplementary exhausts T = diaphragm on channels 1, 3, 5 U = diaphragm in supply 1 J = diaphragm exhausts 3 and 5
G77	SOLENOID MATERIAL: G = PA U = PET

Code



338D-015-02	2 x 3/2 NC	solenoid/spring	internal	2,5 ÷ 10	-	С
348D-015-02	2 x 3/2 NO	solenoid/spring	internal	2,5 ÷ 10	-	Α
398D-015-02	1 x 3/2 NC + 1 x 3/2 NO	solenoid/spring	internal	2,5 ÷ 10	-	G
358-015-02	5/2 monostable	solenoid/spring	internal	2,5 ÷ 10	-	м
358-011-02	5/2 bistable	solenoid/solenoid	internal	1,5 ÷ 10	-	В
368-011-02	5/3 CC	solenoid/solenoid	internal	2÷10	-	н
378-011-02	5/3 CO	solenoid/solenoid	internal	2÷10	-	к
388-011-02	5/3 CP	solenoid/solenoid	internal	2 ÷ 10	-	N
338D-E15-02	2 x 3/2 NC	solenoid/spring	external	-0,9 ÷ 10	2,5 ÷ 10	Q
348D-E15-02	2 x 3/2 NO	solenoid/spring	external	-0,9 ÷ 10	2,5 ÷ 10	R
398D-E15-02	1 x 3/2 NC + 1 x 3/2 NO	solenoid/spring	external	-0,9 ÷ 10	2,5 ÷ 10	S
358-E15-02	5/2 monostable	solenoid/spring	external	-0,9 ÷ 10	2,5 ÷ 10	D
358-E11-02	5/2 bistable	solenoid/solenoid	external	-0,9 ÷ 10	1,5 ÷ 10	Y
368-E11-02	5/3 CC	solenoid/solenoid	external	-0,9 ÷ 10	2÷10	v
378-E11-02	5/3 CO	solenoid/solenoid	external	-0,9 ÷ 10	2 ÷ 10	Z
388-E11-02	5/3 CP	solenoid/solenoid	external	-0,9 ÷ 10	2 ÷ 10	w
CNVL/1L	free position (electrical and pneumatic cover)	-	-	-	-	L
CNVL-3P1	plate for supply and outlets	-	-	-	-	х
CNVL-3H-TP (x1)	diaphragm for supply (1)	-	-	-	-	U
CNVL-3H-TP (x2)	diaphragm for outlets (3-5)	-	-	-	-	1
CNVL-3H-TP (x3)	diaphragm for supply (1) and outlets (3-5)	-	-	-	-	т

Products designed for industrial applications. General terms and conditions for sale are available on www.camozzi.com.

### **MODIFICATION OF A VALVE FUNCTION**

In case a solenoid valve type M is inserted in a free position and a monostable or bistable electrical conveyor is already available, the following components must be ordered:

2x screws Cod. CNVL/21 3x interface seals Cod. CNVL-3H/7N 1x solenoid valve 358-015-02-(G77-U77)

In case a solenoid valve type B is inserted in a free position and a bistable electrical conveyor is already available\*, the following components must be ordered:


1x electrical module with bistable solenoid valve Cod. 3PAC-R-IF1 1x solenoid valve 358-015-02-(G77-U77)

\* In case a monostable conveyor has been already mounted, it must be replaced by a bistable one, provided that the maximum number of 22 signals is not exceeded.

DRAWING NOTE:

A = grey label (monostable)


B = white label (bistable)




Θ

 $\bigcirc$ 


 $\bigcirc$ 








# MULTIPOLE version - DIMENSIONS


Automation











48.9 40 12.5

\_ 22.6

6

0

0 0

Φ

Θ

 $\odot$ 

358

Θ

æ

2

14.0 122

68

۲

0

OUT

01

02

03

04

05

06

PWR

0000

0

IN

25

U æ

Ó

C

①

<u>1</u>

1 30 40

1

ē

В

25

Ū

Q

I C

C

00

Ô

Ō

Ô

Ô ۲

•

Α

26

0

0

Q

26

D

0 0 PWRI PWR2 0 0 DM DM2

للحظين

0

0

۲

60

ĥ

С

D

Ε

R

Т

U ٧ 7 Κ Υ 26

Œ

L.NK

0

0

 $\Theta$ 

0

S

45

6

C

Ć

14.5

¢

 $\oplus$ 

õ

 $\oplus$ 

0

Φ

 $\odot$ 

00

199.1

0

φ

5.5


11.5

0

 $\bigcirc$ 

O

0



coding example 2. N = number of valve positions

DRAWING NOTE:

23

0 ៙

0

O O

Φ

0

O

0

0

Θ

0

O

O 

Ó

1. letters and numbers refer to the details which are reported in the

26 + ( N x 23 )

 $\Box \bar{o}$ 

Ø 0

0

 $\bigcirc$ 

¢ Ó

0

Ø

O

0

8

⊚

0 0

O

O

0

⊜ 0

0

0

O

 $\bigcirc$ O

10


0

0

O


۲


0




Automatio

# FIELDBUS version with EXPANSION MODULE - DIMENSIONS









V Z K Y

# 25-pin Sub-D connector module

Initial module to connect the Intermediate Electrical Modules







Mod. 3PBC-N-XS0

# Intermediate electrical module - 2 positions, mono and bistable



To be mounted with subbases with 2 positions. The type label in correspondence of LEDs is: - grey in monostable intermediate modules - white in bistable intermediate modules







Mod.		
3PAC-M-XI2	Monostable module	
3PAC-R-XI2	Bistable module	


# Intermediate electrical module - 3 positions, mono and bistable



To be mounted with subbases with 3 positions. The type label in correspondence of LEDs is: - grey in monostable intermediate modules - white in bistable intermediate modules







 Mod.


 3PAC-M-XI3
 Monostable module

 3PAC-R-XI3
 Bistable module

# Electrical Module for a bistable solenoid valve



Supplied with: 2x screws for valve mounting 2x screws for solenoid mounting 1x interface seal 2x interface seals for solenoid





VALVE ISLANDS > SERIES 3 PLUG-IN VALVE ISLANDS

End cap for electric module


#### 28,5 11,5 62 DIMENSIONS Mod. 3PAC-R-TP1 Terminal module Mod. CNVL-3H The following is supplied: 2x fixing nuts 0.0. Φ G \$ ø ပ $\sim$ 4 \$ ø 0 М F DIMENSIONS Mod. С D Е F Н T М Ν 0 Р Q G 78 11.5 CNVL-3H 69.5 46 12 29 4.3 14 5 32 3/8 6 Initial/terminal pneumatic Module - 2 positions L1 Supplied with: 3x O-rings В Α Ρ 2x fixing screws 2x junction plugs

DIMENSION	S															E
Mod.	А	В	С	D	Е	F	G	Н	L1	М	Ν	0	Р	Q	R	
CNVL-3H2	23	23	69,5	46	12	29	3/8	78	57,5	4,3	14	5	6	32	7	

5

6

4.3 14 32




# Initial/terminal pneumatic Module - 3 positions




Supplied with: 3x O-rings 2x fixing screws 2x junction plugs 9x interface seals module/valve

6x interface seals module/valve



G



Mod.

DIMENSIONS

CNVL-3H3

А В С D Е F G Н L1 М Ν 0 Р Q R 7

23

23


69,5

12 29 3/8 78 80,5

46



# Intermediate pneumatic Module - 2 positions



С

15

22


Mod.

# Diaphragm for separation channels 1 - 3 - 5



Supplied with: 1x diaphragm.


If you need cod. U, please order N° 1 piece. If you need cod. J, please order N° 2 pieces. If you need cod. T, please order N° 3 pieces.



	13,0	5
CNVL-3H-TP	15.6	6
Mod.	А	В

# CPU Module - pin configuration






Mod.	Coding reference	Fieldbus Protocol	2	1	Bus-IN connector	Bus-OUT connector
CX01-0-0	01	PROFIBUS	Bus-IN	Bus-OUT	M12 B 5 pin male	M12 B 5 pin female
CX02-0-0	02	DeviceNet	Bus-IN	Bus-OUT	M12 A 5 pin male	M12 A 5 pin female
CX03-0-0	03	CANopen	Bus-IN	Bus-OUT	M12 A 5 pin male	M12 A 5 pin female
CX04-0-0	04	EtherNet/IP	Bus-OUT	Bus-IN	M12 D 5 pin female	M12 D 5 pin female
CX05-0-0	05	EtherCAT	Bus-OUT	Bus-IN	M12 D 5 pin female	M12 D 5 pin female
CX06-0-0	06	PROFINET	Bus-OUT	Bus-IN	M12 D 5 pin female	M12 D 5 pin female

# Expansion Module - pin configuration



Note: to connect the Expansion with the subnet, we recommend the use of cables Mod. CS-SB04HB-... or CS-SC04HB-...



Mod.	Coding reference	Fieldbus Protocol	Bus-IN and Bus-OUT connector
CX99-0-0	99	Subnet expansion	M12 D 5 pin female

#### **CPU Module - Characteristics**

It is a slave node of the main PROFIBUS, CANopen, DeviceNet, EtherNet/IP, EtherCAT, PROFINET network and the Master module of the subnet. All modules provided can be connected only on the right side of the CPU module, like the digital/analog inputs/outputs, direct interface modules for the valve islands (Series F, HN and 3) and the initial module of the subnet.

It has its own M12A 4 pin Male connection to supply the modules connected, distinguishing both logic supply and power supply. Two M12 connections for Bus IN and Bus OUT of the main network, which M12 connection will take over the relative specifications according to the choosen protocol.


The addressing is performed by means of the Rotary Switch for the protocols with this feature, while for Ethernet protocols, addressing is performed by means of the protocol itself. Leds indicating the working state. A maximum number of 1024 inputs and 1024 outputs can be managed.



#### **Expansion Module - Characteristics**

At its right side, different modules can be connected like the digital/analog inputs/outputs, the direct interface modules for the valve islands (Series F, HN and 3) and the initial module of the subnet to re-amplify it or to create new branches. It has its own M12 A 4 pin male connection to supply the devices connected, distinguishing both logic supply and power supply. It has two M12 D 5 pin female connections for Bus-IN and Bus-OUT connection of the subnet. Leds indicate the working state.

The valve island equipped with the Expansion Module can be used only in presence of a subnet.



#### Initial subnet module Mod. ME3-0000-SL

This module can be connected only in presence of a CPU or Expansion module and can be mixed with other either digital or analog Input and Output devices. Every subnet can have an extension of maximum 100 metres, with a maximum of 8 interruptions. Up to maximum 5 initial modules can be connected, one aside another or along the subnet in order to create a tree structure, in series or both, in order to optimize the length of the cables and the topology of the subnet in different applications. The module is equipped with the Bus-OUT connection only of subnet type M12 D 4 pin female.






Mod.	Coding reference	Bus-OUT connection	Max number of modules for subnet	Max extension of subnet per module
ME3-0000-SL	S	M12D 4 pin female	5	100 m

#### Sub-D adaptor module 25 pin Mod. CXA-25P



It is an Expansion module of the subnet and can be connected to all valve islands with Sub-D 25 pin connection. It can manage up to a maximum of 24 Output. It has its own M12 A 4 pin male connection for the supply of the valves connected, distinguishing both logic supply and power supply and two M12 D 4 pin female connections for the Bus-IN and Bus-OUT of the subnet. The subnet can have a length of maximum 100 metres. The power of a single Output is 3 W to 24 V DC. Thanks to the PWM technique it is possible to set a power reduction to only maintain operation.



CXA-25P

CXA-37P

Led 1 = Yellow LNK1 Led 2 = Yellow LNK2 Led 3 = Green PWR, supply present and OK

Mod.	Interface	Digital Outs	Bus-IN connection	Bus-OUT connection	PWR connection	Supply	Power for every Output
CXA-25P	Sub-D 25 pin	24	M12D 4 pin female	M12D 4 pin female	M12A 4 pin male	24 V DC	3 W

# Digital input Module Mod. ME3-0800-DC and ME3-0400-DC

The Digital input module can be connected only in presence of a CPU or Expansion module and can be mixed with other either digital or analog Input and Output devices and with the initial module of the subnet.

It has 8 or 4 M8 3 pin connections.



4	
3000	1

Mod.	Coding reference	Number of digital inputs	Connection	Number of connectors	Dimensions	Signalling	Sensor supply	Overvoltage protection	Absorption	Type of signal	Protection class	Operating temperature	Weight
ME3-0800-DC	А	8	M8 3 pin female	8	122 x 25 mm	1 yellow led for each input	24 V DC	400 mA for 4 sensors	10 mA	PNP	IP65	0 ÷ 50°C	110 g
ME3-0400-DC	В	4	M8 3 pin female	4	122 x 25 mm	1 yellow led for each input	24 V DC	400 mA for 4 sensors	10 mA	PNP	IP65	0 ÷ 50°C	110 g

#### Analog input/output module Mod. ME3-\*\*\*\*-AL

The analog input/output module can be connected only in presence of a CPU or Expansion module and can be mixed with other either digital or analog Input and Output devices and with the initial module of the subnet. It has two M12 A 5 pin female connections and it can be configured as 2 analog Outputs or 2 Inputs or 1 Input + 1 Output. Every analog outputs or input has a 12 bit resolution for both inputs and outputs available in the versions from 0-10 V DC and from 4-20mA. The refreshment time of the analog devices is submitted to the delay of the subnet and therefore to its topology. An average delay is less than 6 ms, to which the delay of the main network managed by the PLC has to be added.





Mod.	Coding reference	Number of analog inputs	Number of analog outputs	Connection
ME3-C000-AL	C	2 inputs 4-20 mA	-	2x M12 A 5 pin female
ME3-D000-AL	D	2 inputs 0-10 V	-	2x M12 A 5 pin female
ME3-E000-AL	E	1 input 4-20 mA + 1 input 0-10 V	-	2x M12 A 5 pin female
ME3-00U0-AL	U	-	1 output 4-20 mA + 1 output 0-10 V	2x M12 A 5 pin female
ME3-00R0-AL	R	-	2 outputs 4-20 mA	2x M12 A 5 pin female
ME3-00T0-AL	Т	-	2 outputs 0-10 V	2x M12 A 5 pin female
ME3-00Z0-AL	Z	1 input 4-20 mA	1 output 4-20 mA	2x M12 A 5 pin female
ME3-00K0-AL	К	1 input 0-10 V	1 output 0-10 V	2x M12 A 5 pin female
ME3-00V0-AL	V	1 input 0-10 V	1 output 4-20 mA	2x M12 A 5 pin female
ME3-00Y0-AL	Y	1 input 4-20 mA	1 output 0-10 V	2x M12 A 5 pin female

# Digital power output module Mod. ME3-0004-DL

The digital output module can be connected only in presence of a CPU or Expansion module and can be mixed with other either digital or analog Input and Output devices and with the initial module of the subnet. It has two M12 A 5 pin female connections, each connection can manage 2 digital outputs and can provide a maximum of 10 W to 24 V DC. The device is useful to pilot a bistable valve or two monostable valves for each connector, or to activate the electric coils or other electric devices with maximum absorption of 10 W to 24 V DC. Connecting two outputs to one electric device only and activating them simultaneously, it is possible to provide maximum 20 W to 24 V DC.





Mod.	Coding reference	Number of digital outputs		Number of connectors	Dimensions	Signalling		Max power for M12 connector		Type of signal	Protection class	Operating temperature	Weight
ME3-0004-DL	Q	4	M12 A 5 pin female	2	122 x 25 mm	1 yellow led for each output	24 V DC	20 W	10 W	NPN	IP65	0 ÷ 50°C	100 g

Pneumatic/electric interface Module for Fieldbus version




Supplied with: 1x module with card 1x foot for manifold

VALVE ISLANDS > SERIES 3 PLUG-IN VALVE ISLANDS

# Adaptor and panel mount for Ethernet RJ45 to M12 D networks






Mod.	description	type of connector	connection	cable length (m)
CS-SE04HB-F050	moulded cable	straight	RJ45 male, M12 D 4 pin female - Pin 5 is not connected	0.5

# Profibus-DP data line tee






Mod.

# CANopen / DeviceNet data line tee







CS-AA05EC

# M12 male terminating resistor

For PROFIBUS, CANopen, DeviceNet








Mod.	description	type of connector	connection	Protocol
CS-MQ05H0	moulded terminating resistor	straight	M12 B 4 pin male - Pin 5 is not connected	PROFIBUS
CS-LP05H0	moulded terminating resistor	straight	M12 A 5 pin male - Pin 5 is connected	CANOpen / DeviceNet

SERIES 3 PLUG-IN VALVE ISLANDS

Subnet terminating resistor



Mod.	description	type of connector	connection	Protocol
CS-LF05HC	for wiring	straight	M12 A 5 pin female	CANopen / DeviceNet
CS-MF05HC	for wiring	straight	M12 B 5 pin female	PROFIBUS




CS-LF05HC

C S-MF05HC

VALVE ISLANDS > SERIES 3 PLUG-IN VALVE ISLANDS


#### Angular 90° female M12 connectors for Bus-IN





Mod.	description	type of connector	connection	Protocol
CS-LR05HC	for wiring	90°	M12 A 5 pin female	CANopen / DeviceNet
CS-MR05HC	for wiring	90°	M12 B 5 pin female	PROFIBUS

# Straight male M12 connectors for Bus-OUT



Protocol


CANopen / DeviceNet

PROFIBUS

### Angular 90° male M12 connectors for Bus-OUT



The Mod. CS-LSO5HC can also be used for the connection of the digital output modules and of the analog input and output modules.



5 pin male straight M12 DUO connector

type of connector

90°

90°

description

for wiring

for wiring



Mod.

CS-LS05HC


CS-MS05HC

For the connection of the digital output modules and analog input/output modules.

connection

M12 A 5 pin male

M12 B 5 pin male








Mod.	description	type of connector	connection	cable length (m)
CS-LD05HF	for wiring	straight	M12 A 5 pin male	-

# 5 pin male angular M12 DUO connector




Mod. description type of connector connection L [ cable length ] (m) CS-DW03HB-C250 moulded cable straight M8 3 poli male / female 2.5 moulded cable CS-DW03HB-C500 M8 3 pin male / female straight 5

32

34

# USB to Micro USB cable Mod. G11W-G12W-2






Mod.	description	connections	material for outer sheath	cable length "L" (m)
G11W-G12W-2	black shielded cable 28 AWG	standard USB to Micro USB	PVC	2

For the hardware configuration of the Camozzi products

# Adapter cable, M8 3-pin male - M12 4-pin female






Mod.	description	max voltage	max current	Nr conn. wires	connections	outer sheath	cable "L (m)
CS-AG03HB-C250	3-pin cable 24 AWG, high flexibility	50V AC / 60V DC	3 A	3	M8 3-pin male - M12 4-pin fem.	PUR black	2.5
CS-AG03HB-C500	3-pin cable 24 AWG, high flexibility	50V AC / 60V DC	3 A	3	M8 3-pin male - M12 4-pin fem.	PUR black	5



# Straight Sub-D 25 pin female connector with axial cable

#### Protection class IP65






β	PIN	cable length (m)
7.7	16	3
7.7	16	5
7.7	16	10
7.7	16	15
7.7	16	20
7.7	16	25
9	25	3
9	25	5
9	25	10
9	25	15
9	25	20
9	25	25
	7.7 7.7 7.7 7.7 7.7 7.7 7.7 9 9 9 9 9 9	7.7       16         7.7       16         7.7       16         7.7       16         7.7       16         7.7       16         7.7       16         7.7       16         7.7       16         9       25         9       25         9       25         9       25         9       25         9       25         9       25         9       25

# Right angle Sub-D 25 pin female connector with axial cable

#### Protection class IP65






Mod.	۵	PIN	cable length (m)
G3X1-3	7.7	16	3
G3X1-5	7.7	16	5
G3X1-10	7.7	16	10
G3X1-15	7.7	16	15
G3X1-20	7.7	16	20
G3X1-25	7.7	16	25
G4X1-3	10	25	3
G4X1-5	10	25	5
G4X1-10	10	25	10
G4X1-15	10	25	15
G4X1-20	10	25	20
G4X1-25	10	25	25

# Cable with straight connectors

VALVE ISLANDS > SERIES 3 PLUG-IN VALVE ISLANDS

For PROFINET, EtherCAT, EtherNet/IP and subnet






Mod.	description	type of connector	connection	L [ cable length ] (m)
CS-SB04HB-D100	moulded cable	straight	2x M12 D 4 pin male	1
CS-SB04HB-D500	moulded cable	straight	2x M12 D 4 pin male	5
CS-SB04HB-DA00	moulded cable	straight	2x M12 D 4 pin male	10
CS-SB04HB-DD00	moulded cable	straight	2x M12 D 4 pin male	15
CS-SB04HB-DG00	moulded cable	straight	2x M12 D 4 pin male	20
CS-SB04HB-DJ00	moulded cable	straight	2x M12 D 4 pin male	25

# Cable with 90° angular connectors



For PROFINET, EtherCAT, EtherNet/IP and subnet


Mod.	description	type of connector	connection	L [ cable length ] (m)
CS-SC04HB-D100	moulded cable	90°	2x M12 D 4 pin male	1
CS-SC04HB-D500	moulded cable	90°	2x M12 D 4 pin male	5
CS-SC04HB-DA00	moulded cable	90°	2x M12 D 4 pin male	10
CS-SC04HB-DD00	moulded cable	90°	2x M12 D 4 pin male	15
CS-SC04HB-DG00	moulded cable	90°	2x M12 D 4 pin male	20
CS-SCO4HB-DJOO	moulded cable	90°	2x M12 D 4 pin male	25



# M8 and M12 connector cover caps



For digital and analog input/output modules and subnet



Mod.	А	В	C [ Connection ]
CS-DFTP	10	11	M8
CS-LFTP	13.5	13	M12


# Mounting brackets for DIN rail



DIN EN 50022 (mm 7,5 x 35 - width 1) Supplied with:

2x plates 2x screws M4x6 UNI 5931





Mod. PCF-E520