
# Series Y valve islands, Individual, Multipole and Fieldbus

Valve island with integrated Pneumatics and Electronics. Available versions: Individual, Multipole, Fieldbus (Profibus-DP, DeviceNet, CANopen). Valve functions: 2x2/2; 2x3/2; 5/2; 5/3 CC



Series Y solenoid valves are based on particular solutions regarding both the pneumatic, as well as the electronic part.

Sub-bases and valve bodies are integrated in a sole "module". Different kinds of cartridges and spools are inserted in the module to configure the desired valve function. The valve island can be expanded and modified and its maintenance is easy and safe.

Several solutions are possible for the electric connection through the use of modules for digital electric inputs.

Manuals, instruction sheets and configuration files can be found on catalogue.camozzi.com or on the QR code on the lable of the product.

- » Pneumatic modularity: 2, 4, 6 and 8 valve positions
- » Valve size: 12,5 mm
- » Flow rate: 800 Nl/min

### **GENERAL AND ELECTRICAL DATA**

VALVE ISLANDS > SERIES Y VALVE ISLANDS

Enclosed in the package there is a label on which it is possible to write each individual coil number.

PNEUMATIC SECTION	
Valve construction	Spool with seals
Valve functions	5/2 monostable and bistable 5/3 CC 2 × 2/2 NC 2 × 2/2 NO 1 × 2/2 NC + 1 × 2/2 NO 2 × 3/2 NC 2 × 3/2 NC
	1 x 3/2 NC + 1 x 3/2 NO
Materials	Aluminium spool brass cartridge seals in NBR end covers and covers in technopolymer
Connections	Outlets 2 and 4: G1/8 Inlets 1 and 11: G1/4 Pilot ports: 12/14 and respective exhaust 82/84 G1/8 Exhausts 3/5: G1/2
Temperature	0 ÷ + 50°C
Air specifications	Filtered compressed air, non lubricated, class 3.4.3 according to ISO 8573.1 standard. If lubrication is necessary, please use only oils with maximum viscosity of 32 Cst and the version with external servo-pilot supply. The servo-pilot supply air quality class must be 3.4.3 according to ISO 8573.1 standard.
Dimensions/size	12.5 mm
Working pressure	-0.9 ÷ 10 bar (with external servo pilot supply)
Pilot pressure Flow rate	3 ÷ 7 bar 800 NI/min
	000 Nt/11111
INLETS SECTION	
Voltage	24 V ±10%
Max current	350 mA
Operating temperature	0°C ÷ +50°C
Relative humidity	30-90% +25°C 30-50% +50°C
Conform with standards	EN 61131-2 EN 61000-6-2 EN 61000-6-4
Protection class	IP65
Max. number of connected inlets	48
Max. number of connected Inlet Modules	3
Max. distance between init. mod. and last input or expansion mod.	50 m
Max. cable length between sensor and input module	30 m
ELECTRICAL SECTION	
Voltage	24V±10%
Max. absorption	1300mA continuous 1600 mA latch
Operating temperature	0°C ÷ +50°C
Continuous current	ED 100%
Protection class	IP50 Individual version IP65 Multipole version PNP IP65 Fieldbus versions
Baud rate	Profibus-Dp 12 Mbit/s EN 50170 DeviceNet 500 Kbit/s EN 50235 CAN open 500 Kbit/s EN 50235
Maximum number of nodes	Profibus-Dp 32/127 DeviceNet 64 CAN open 127
Maximum number of expansions per node	15
Max. length of internal Fieldbus	50 m
Relative humidity	30-90% +25°C 30-50% +50°C
Conform with standards	EN 61326-1 EN 61010-1
Max. number of solenoids connected/activated at the same time	32


Products designed for industrial applications. General terms and conditions for sale are available on www.camozzi.com.



- one or more pneumatic modules with either 2, 4, 6 or 8 valve positions incorporating the sub-base with two separated channels for supply and exhaust, and the seat for the valves. It is possible to join the different modules together with pins and fixing screws, thus increasing the number of valve positions;

- two terminal plates (right and left) on which it is possible to connect pressure inlets and exhausts;

- seals among the various elements;
- cartridges and spools which reproduce the different valve functions (further information on the following pages)
- one or more covers which integrate electronics and pilots distributing signals to valves (further information on the following pages)




### Plate for supplementary supply and exhaust

The two independent supplies allow the same valve to have different pressure values on outlets 2 and 4.

In this way a higher pressure can be used for the working operations and a lower pressure for the repositioning of the actuators, reducing the costs for generating compressed air.

The modularity of 2, 4, 6 or 8 valve positions allows, through the specific seals, to subdivide the island in pressure/exhaust zones without loosing valve positions. Functions W or X can be used to supply the intermediate pressure zones of an island.

To avoid any possible problem during exhaust, the exhaust itself has been increased and it passes through on both sides.





### Air specifications - filtering elements

To guarantee a proper air quality and to not compromise the functioning of the valves, we advise to adopt filtering elements according to class 3 of table DIN ISO 8573-1.

Filter models: MC104-F10 MC238-F10 MC202-F10 N108-F10 N104-F10






AIR QUALI	AIR QUALITY CLASS ACCORDING TO STANDARD DIN ISO 8573-1						
Class	Solid bodies Max. dimension of the particles	Water contents dew-point	Oil quantity max. concentration mg/m <sup>3</sup>				
1	0,1 μ	-70°C	0,01				
2	1μ	-40°C	0,1				
3	5 μ	-20°C	1				
4	15 μ	+3°C	5				
5	40 μ	+7°C	25				

### Connection by means of terminal plates

The connection to the compressed air source by means of terminal plates enables different types of connection. The fitting Mod. 6512 \* (for dimensions see section 4/1.05) can be connected to inlets 2 and 4.




\* It is possible to connect the following fittings, supplied with 0-ring: 6512-4-1/8-M 6512-6-1/8-M 6512-8-1/8-M

Supply (1-11)	Exhaust (3/5)	Servo-pilot supply (12/14)	Servo-pilot exhaust (82/84)	Inlets (2-4)
G1/4	G1/2	G1/8	G1/8	G1/8

Products designed for industrial applications. General terms and conditions for sale are available on www.camozzi.com

### TERMINAL PLATES - pneumatic connections from left and right




# SERIES Y VALVE ISLANDS

utomatio


Terminal Plates	Terminal Plates					
Code	Common connections	Separated connections				
А	1-11 12/14	82/84 3/5				
В	1-11	12/14 82/84 3/5				
C	-	1-11 12/14 82/84 3/5				

# TERMINAL PLATES - pneumatic connections from the right




Terminal Plates					
Code	Common connections	Separated connections			
D	1-11 12/14	82/84 3/5			
E	1-11	12/14 82/84 3/5			
F	-	1-11 12/14 82/84 3/5			

### TERMINAL PLATES - pneumatic connections from the left



Terminal Plates		
Code	Common connections	Separated connections
G	1-11 12/14	82/84 3/5
н	1-11	12/14 82/84 3/5
1	-	1-11 12/14 82/84 3/5

### Available functions



Code	Function	Actuation/return	Working pressure (bar)	Pilot pressure (bar)	Symbol
М	5/2 Monostable	solenoid/pneumatic spring	-0,9 ÷ 10	3 ÷ 7	М
В	5/2 Bistable	solenoid/solenoid	-0,9 ÷ 10	3 ÷ 7	В
v	5/3 Centres Closed	solenoid/solenoid	-0,9 ÷ 10	3 ÷ 7	V
I	2 x 2/2 (1 NO + 1 NC)	solenoid/solenoid	-0,9 ÷ 10	3 ÷ 7	I
E	2 x 2/2 (NC )	solenoid/solenoid	-0,9 ÷ 10	3 ÷ 7	E
F	2 x 2/2 (NO )	solenoid/solenoid	-0,9 ÷ 10	3 ÷ 7	F
G	2 x 3/2 (1 NO + 1 NC )	solenoid/solenoid	-0,9 ÷ 10	3 ÷ 7	G
С	2 x 3/2 (NC )	solenoid/solenoid	-0,9 ÷ 10	3 ÷ 7	С
Α	2 x 3/2 ( NO )	solenoid/solenoid	-0,9 ÷ 10	3 ÷ 7	А
L	Free position	-	-	-	L
w	Additional supply from 2 and 4	-	-	-	W
т	Diaphragm seal (module's separation)	-	-	-	Т
Р	Through seal (module's separation)	-	-	-	Р
T/	Diaphragm seal (separation of both modules and covers)	-	-	-	Т
P/	Through seal (separation of both modules and covers)	-	-	-	Р
U	Diaphragm seal 3/5 open	-	-	-	U
н	Diaphragm seal 3/5 - 11 open	-	-	-	Н
N	Diaphragm seal 1 - 11 open	-	-	-	N
U/	Diaphragm seal 3/5 open (separation of both modules and covers)	-	-	-	U
К	Expansion module, 2 positions with 3/5 - 11 closed	-	-	-	К
R	Expansion module, 2 positions with 3/5 - 1 - 11 closed	-	-	-	R
0	Expansion module, 2 positions with 1-11 closed	-	-	-	0
Q	Expansion module, 2 positions with 3 - 5 closed	-	-	-	Q
х	Module for additional supply	-	-	-	Х

### Cartridges and spools for the creation of valve functions


The different valve functions are obtained by inserting the cartridges and spools in the seats of the pneumatic module. These seats have been designed at right angles with respect to the terminal plates.


The shape of cartridges and spools depends on the valve function required.

Example: (A) = Cartridge and spool for a 3/2-way function (B) = End cover

(C) = Cartridge and spool for a 5/2-way function

The modification or maintenance of a valve position is obtained removing the end cover "B" and replacing both the cartridge and the spool. During modification/maintenance, the tubing for the pneumatic connection can stay connected to the island, thus simplifying and optimising the whole operation.










### Individual version - dimensions





n = number of valves n1 = number of supplementary power supply modules (cod. X)











Products designed for industrial applications. General terms and conditions for sale are available on www.camozzi.com.

### Covers

The Multipole and Fieldbus versions use covers for the pilot valves, which guarantee the IP65 protection class as well as the mechanical protection of internal parts. The covers combine:

- manual override in the monostable and bistable functions. A simple pressure is enough to obtain a monostable function,
- whereas the bistable function is obtained coupling a rotation.
- LEDs for the voltage signalling on the coil
- diagnostic LEDs on Fieldbus versions
- ports for the electrical connectors

VALVE ISLANDS > SERIES Y VALVE ISLANDS

- integrated electronic boards
- connection interface with the pilot valves
- outlet protection against overvoltage, reversed polarity and short circuit
- connections realized on printed circuit boards




### Covers - Multipole version

The Multipole cover is available in three sizes and allows the connection to valve islands with 4, 6 or 8 valve positions. Every position can be freely equipped with either monostable or bistable solenoid.

It is possible to join two or more valve islands placing a plate for intermediate supply, type "X", under every Sub-D plug.

Pneumatic modules can be composed of 2, 4, 6 or 8 valve positions and separated by various seals.

A module for additional supply type "X" or a function "W" must be always inserted between two seals separating channels 1 and 11.





### Multipole version - dimensions

0

10,


(0)


0


lo,

















### **Covers - Fieldbus version**


This version allows the direct connection to Profibus-Dp, DeviceNet, CANOpen. The main feature of this version is a starting module called "Initial module" to which the subfieldbus is connected for the management of the expansion modules. The Initial module can arrange up to 32 solenoids (outputs) and 48 inlets.

To optimize the electronic part, a proper function allows the remoting of unused outlets on the expansion modules. It is thus possible to pilot 32 solenoids on 32 valve positions without loosing any output signal. Advantages:

- cost reduction thanks to a reduced number of initial modules that can be replaced by expansion modules;
 - simplified code as the type of subbase is the same for bistable or monostable solenoid valves;

- saving of electrical signals that are not consumed by free positions and/or diaphragm seals;

- reduced dimensions, simplified connections and optimization of installation costs thanks to the covers modular structure which allows several islands to be joined together.



utomatio

### Fieldbus Initial Module - characteristics

The initial module has always 8 positions.

It is only the initial module to which the Fieldbus and electrical supply (24V DC) is connected.

The coils addressing can be sequential or customized by a specific configuration software that can be downloaded from our website http://catalogue.camozzi.com/Downloads, as well as the configuration file.

Pneumatic modules, available with 2, 4, 6, or 8 valve positions, can be separated by proper seals and allow the creation of different pressure/exhaust zones.



### Fieldbus Expansion Module - characteristics


Versions available: 2 valve positions 4 valve positions 8 valve positions

The expansion modules: - communicate among themselves and with the initial module through the Cam.I.Net subfieldbus. - can be easily added to enlarge the valve island, thus avoiding the use and costs of free positions;

- can be positioned up to 50 metres from initial module and subdivided into up to 15 groups.

The particular construction of the islands allows the in-line mounting of all the Expansion modules.

Pneumatic modules, available with 2, 4, 6, or 8 valve positions, can be separated by proper seals and allow the creation of different pressure/exhaust zones.



### Electrical digital inputs module ME-1600-DL\* - Characteristics

It allows the connection of 16 electrical input signals via 8 M12 DUO 5 poles connections. It is thus possible to connect 2 inputs for each connection.

The input module can be positioned at any point of the Cam.I.Net. sub-fieldbus.


3 input modules at most can be connected to the initial module, for a total of 48 inputs.

\* not for the DeviceNet version



### Digital Inputs Module ME-1600-DL\* - dimensions

\* not for the DeviceNet version



Ā



Dimensions don't change according to the different Fieldbus versions (Profibus-DP, CANopen, DeviceNet).



E

0

0

0


0

0

0

0


0





Auto


### Fieldbus Expansion Module with 8 valve positions - dimensions


















### Fieldbus Expansion Module with 4 valve positions - dimensions

















VALVE ISLANDS > SERIES Y VALVE ISLANDS


### Fieldbus Expansion Module with 2 valve positions - dimensions















### CODING



1 2 3 YP1 - 3

### 1 2 3 YP1M- 8MPXP8B-C

Type of electrical connection	(1)	Type of valve	(2)	Type of terminal plates	(3)
Individual	к	-		-	
Multipole (PNP)	М	-		-	
Profibus-Dp	Р	-		-	
DeviceNet	D	-		-	
CANopen	С	-		-	
Expansion	E	-		-	
-		5/2 Monostable	М	-	
-		5/2 Bistable	В	-	
-		5/3 CC	v	-	
-		2 × 2/2 1 NO + 1 NC	I	-	
-		2 x 2/2 NC	E	-	
-		2 x 2/2 NO	F	-	
-		2 x 3/2 1 NO + 1 NC	G	-	
-		2 x 3/2 NC	С	-	
-		2 x 3/2 NO	А	-	
-		Free position	L	-	
-		Additional supply module from 2 and 4	w	-	
-		Diaphragm seal (modules separation)	т	-	
-		Through seal (modules separation)	Р	-	
-		Diaphragm seal (modules and cover separation)	T/	-	
-		Through seal (modules and cover separation)	P/	-	
-		Diaphragm seal 3/5 opened	U	-	
-		Diaphragm seal 3/5-11 opened	н	-	
-		Diaphragm seal 1-11 opened	N	-	
-		Diaphragm seal 3/5 opened, modules and cover separ.	U/	-	
-		Module with 2 positions and 3/5-11 closed	К	-	
-		Module with 2 positions and 3/5-1-11 closed	R	-	
-		Module with 2 positions and 1-11 closed	0	-	
		Module with 2 positions and 3/5 closed	Q	-	
-		Additional supply module	х	-	
-		-		in common 1/11 - 12/14 individual 82/84 - 3/5	Α
-		-		in common 1/11 individual 12/14 - 82/84 - 3/5	В
-		-		individual 1/11 - 12/14 - 82/84 - 3/5	С
-		-		in common 1/11 - 12/14 individual 82/84 - 3/5	D
-		-		in common 1/11 individual 12/14 - 82/84 - 3/5	E
-		-		individual 1/11 - 12/14 - 82/84 - 3/5	F
-		-		in common 1/11 - 12/14 individual 82/84 - 3/5	G
-		-		in common 1/11 individual 12/14 - 82/84 - 3/5	н
-		-		individual 1/11 - 12/14 - 82/84 - 3/5	1
-		-		modules without terminal plate	z




### Coding example 1

Valve island with Profibus-DP connection made of: 4x solenoid valves type M 1x diaphragm seal Mod. T 4x solenoid valves type B Terminals with 1 and 11 in common on both sides and 12 /14 separated.

Code: YP1P-4MT4B-B

For the code composition see the coding table on the previous page.





### Coding example 2

Valve island with Multipole connection made of: 4x solenoid valves type M 1x diaphragm seal Mod. T for the separation of pressure zones 4x solenoid valves type B 1x through-out seal Mod. P 1x intermediate additional supply module Mod. X 1x through-out seal Mod. P Terminals with individual connection 4x solenoid valves type C 1x diaphragm seal Mod. T for the separation of pressure zones 4x solenoid valves type M

### Code: YP1M-4MT4BPXP4CT4M-C

For the code composition see the coding table on the previous page.






### Sub-D adaptor module 25 pin Mod. CXA-25P



It is an Expansion module of the subnet and can be connected to all valve islands with Sub-D 25 pin connection. It can manage up to a maximum of 24 Output. It has its own M12 A 4 pin male connection for the supply of the valves connected, distinguishing both logic supply and power supply and two M12 D 4 pin female connections for the Bus-IN and Bus-OUT of the subnet. The subnet can have a maximum length of maximum 100 metres. The power of a single Output is 3 W to 24 V DC. Thanks to the PWM technique it is possible to set a power reduction to only maintain operation.





Led 1 = Yellow LNK1 Led 2 = Yellow LNK2 Led 3 = Green PWR, supply present and OK

Mod.	Interface	Digital Outs	Bus-IN connection	Bus-OUT connection	PWR connection	Supply	Power for every Output
CXA-25P	Sub-D 25 pin	24	M12D 4 pin female	M12D 4 pin female	M12A 4 pin male	24 V DC	3 W

### 25M-25F Sub-D adaptor










 Mod.
 description
 type of connector
 connection
 cable length (m)

 G2X-G2W
 moulded adaptor
 in line
 Sub-D 25 pin female - Male


### Profibus-DP data line tee






Mod.

VALVE ISLANDS > SERIES Y VALVE ISLANDS












Mod.	description	type of connector	connection	Protocol
CS-SU04H0	moulded terminating resistor	straight	M12 D 4 pin	subnet

### Terminal resistance Cam.I.Net

Connector with sub-serial terminal resistance









Mod. CS-FP05H0


### Straight connector for power supply






### Angular 90° female M12 connectors for Bus-IN

0		



Mod.	description	type of connector	connection	Protocol
CS-LR05HC	for wiring	90°	M12 A 5 pin female	CANopen / DeviceNet
CS-MR05HC	for wiring	90°	M12 B 5 pin female	PROFIBUS

### 5 pin male straight M12 DUO connector




	For the connection		ut modules.	Ø20	43.5	
description	type of connector	connection	cable length (m)	l	<u> </u>	

Mod.	description	type of connector	connection	cable length (m)
CS-LH05HF	for wiring	90°	M12 A 5 pin male	-

### M8 and M12 connector cover caps



For digital and analog input/output modules and subnet



Mod.	А	В	C [ Connection ]
CS-LFTP	13.5	13	M12

### Connector Mod. 121-8.. for Individual version






Mod.	description	colour	L = cable length (mm)	cable holding
121-803	crimped cable	black	300	crimping
121-806	crimped cable	black	600	crimping
121-810	crimped cable	black	1000	crimping
121-830	crimped cable	black	3000	crimping



### Straight Sub-D 25 pin female connector with axial cable

### Protection class IP65






Mod.	A	PIN	cable length (m)
G3X-3	7.7	16	3
G3X-5	7.7	16	5
G3X-10	7.7	16	10
G3X-15	7.7	16	15
G3X-20	7.7	16	20
G3X-25	7.7	16	25
G4X-3	9	25	3
G4X-5	9	25	5
G4X-10	9	25	10
G4X-15	9	25	15
G4X-20	9	25	20
G4X-25	9	25	25

# Right angle Sub-D 25 pin female connector with axial cable

### Protection class IP65






Mod.	ø	PIN	cable length (m)
G3X1-3	7.7	16	3
G3X1-5	7.7	16	5
G3X1-10	7.7	16	10
G3X1-15	7.7	16	15
G3X1-20	7.7	16	20
G3X1-25	7.7	16	25
G4X1-3	10	25	3
G4X1-5	10	25	5
G4X1-10	10	25	10
G4X1-15	10	25	15
G4X1-20	10	25	20
G4X1-25	10	25	25

### Programming cable




Manuals, configurator and configuration files are available on our website http://catalogue.camozzi. com in the section Downloads.



 Mod.
 cable length (m)

 CS-FZ03AD-C500
 5


### USB SERIAL converter for programming cable




### Expansion cable




Mod.	cable length (mt)	
CS-FW05HE-D025	0,25	
CS-FW05HE-D100	1	
CS-FW05HE-D250	2,5	
CS-FW05HE-D500	5	
CS-FW05HE-DA00	10	



### Interface with 8 valve positions





Mod. YA1K-N8


### Interface with 6 valve positions




Outlets 2 and 4 are located in the lower part of the module and can be oriented on end-covers side using this interface sub-base.

Supplied with: 1x interface 6 pos. 6x screws M3x25 UNI 5931 12x interface seals

ing this interface sub-base.



G1/8




Mod. YA1K-N6

### Interface with 4 valve positions




Outlets 2 and 4 are located in the lower part of the module and can be oriented on end-covers side using this interface sub-base.




 $\mathcal{O}$ 

50

G1/8








Supplied with:

1x interface 4 pos. 4x screws M3x25 UNI 5931 8x interface seals


### Interface with 2 valve positions

Outlets 2 and 4 are located in the lower part of the module and can be oriented on end-covers side using this interface sub-base.

Supplied with: 1x interface 2 pos. 2x screws M3x25 UNI 5931 4x interface seals



### Intermediate plate for supplementary supplies and exhausts cod. X



Mod.	1	3/5	11
YA1K-N1X/1	G1/4	G3/8	G1/4


00

22

### Solenoid valve Mod. KN000-303-KY3N - spare part for Series Y





Supplied with: 1x interface seal 2x screws M1.6x16 UNI 10227






### Mounting solutions on DIN EN 50022 rail






Wall mounting solutions



### Vertical foot



Supplied with: 2x vertical feet 2x screws M4x10 UNI 5931




Mod.
YA1K-B2

### Horizontal foot



Supplied with: 2x horizontal feet 2x screws M4x14 UNI 5931






### Mounting brackets for DIN rail

DIN EN 50022 (7,5mm x 35mm - width 1)



Supplied with: 2x plates 2x screws M4x6 UNI 5931





DIMENSIONS
Mod.
PCF-E520